



Easy to Use:

Discharge static from your body by touching a grounded metal object.

Press the "ZERO" button twice. From a distance, point the electrode in the direction of the target and move toward it, observing the value on the LCD window.

Press and hold the "PWR ON/HOLD" button and note reading from 1/10" to 8.5", making sure to properly multiply reading according to chart in the user manual. See manual for details.

Product #350 includes carrying case, 9-volt battery, and NIST-traceable calibration certificate.



Measure electrostatic charges with precision!

The ACL 350 is the ideal electrostatic locator meter for applications in which a precise measurement is required. The 3.5 digit LCD displays both negative and positive polarities. By spacing the meter from 1/10" to 8.5", a range of o-80,000 volts can be measured. Utilizing the "HOLD" function allows the user time to record the precise voltage. Easy to use and lightweight, this battery-powered meter can be quickly re-zeroed, allowing for repetitive measurements. The ACL 350 can be used for determining the source of electrostatic charges in ESD-controlled environments or in other areas where static is of concern. It is perfect in electronic component production and assembly areas, textiles, packaging, engineering labs, and printing.

- Accuracy: ± 10%
- Range: o ± 80,000 volts
- **B** Low battery indication
- **B** Powered by 9-volt battery
- **Quick zero function**
- 🕸 1" spacer
- **#** Hold function
- Automatic shut off after 90 seconds
- **Weight: 5 ounces**
- **Size: 4.2" x 2.4" x 0.9"**





ACL Staticide

840 W. 49th Place · Chicago, IL 60609 800.782.8420 · 847.981.9212 · fax 847.981.9278 info@aclstaticide.com · www.aclstaticide.com



ACL Inc. registered to ISO-9001: 2008 Certificate No. 10002746